




WINDING MACHINES

MANUAL COIL WINDER



DL 1010B

To be fixed to the bench, it allows the manual winding of motor coil or of linear windings without wire guide. Complete with a 300 mm diameter faceplate, a pair of square mandrels, a pair of 6 grooves straight arbors, 60 mm diameter, a central arbor for linear winding and a 5 digit revolution counter.

BOBBIN HOLDER WITH COLUMN



DL 1010D

Column to be fixed to the bench, complete with bobbin holder with wire stretcher and two regulating springs. Suitable for wires from 0.2 to 1.5 mm of diameter. It is suggested as an accessory for the manual coil winder DL 1010B.
